



4-POINT 6T Dieless C-Head Battery
Crimper, Pro Bag, No Batt/Chgr, Makita
Power

By Burndy
Catalog # [PAT4PC834LILCBPB](#)

PATRIOT® 4-POINT® Series, 6-Ton Dieless C-Head Battery
Crimper, Pro Bag, No Batteries, Makita Power



Features

- Dieless System with range taking capabilities
- 360° head rotation
- 1.06" Jaw opening
- Overmolded handle for comfort and improved grip
- Ergonomically balanced

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Conductor

Crimping Ranges Copper Terminals: #8-1000
 kcmil
 Copper Splices: #8-500 kcmil
 Copper Flex Terminals: #8-777.7
 Flex
 Copper Flex Splices: #8-500
 kcmil
 Aluminum Terminals: #8-750
 kcmil
 Aluminum Splices: #8-350
 kcmil*
 *1.06" barrel diameter
 maximum for aluminum splices
 due to jaw opening
 Aluminum HYPLUG™: #8-750
 kcmil

Current

Operating Voltage 18 VDC

Dimensions

Length 15.62 in
Weight 12.50 lb.
Height 14.1 in
Width 3.25 in
Dimensions 15.62 in x 3.25 in x 14.1 in

Force Related

Crimp Force Capacity 6 ton

General

Application - For Use On Copper, Aluminum Terminals
 and Splices, HYPLUG™
Trade Name PATRIOT® 4-POINT®
Series PATRIOT® 4-POINT® Series
Tool Type Battery Actuated Crimper
Container Type Nylon Pro Bag
Die Type Dieless
UPC 621945561960
Type Crimper
UPC 12 Digit 621945561960

Logistics

Minimum Pack Quantity 1
Package Contents Crimper, Lanyard, Nylon Pro
 Bag
Pallet Quantity 12
Carton Quantity 1

Operational

Battery Type No Batteries Included (Accepts
 2.0Ah-6.0Ah Makita LI
 Batteries)
Power Source No Charger

Product Assets

[Catalog \[English\]](#)