



6T, BG/D3 Crimp Jaw, Hard Case, 3Ah Makita Batteries

By Burndy
Catalog # [PAT500SJ6LI](#)

PATRIOT® Series, 6-Ton Scissor Action, BG/D3 Crimp Jaw, Hard Case, 3.0Ah Makita Batteries

Features

- Interchangeable scissor action crimping and cutting jaws available
- 180° Head rotation
- Pistol style body
- Uses W and X dies
- Ergonomically balanced

Application

Crimping and Cutting

Specifications

Standards - RoHS Compliance UI
Status

Conductor

- Crimping Ranges
- Copper: #10 sol. - 500 kcmil
 - Copper Flex: #8 AWG - 350 kcmil
 - Aluminum: #14 sol. - 350 kcmil
 - ACSR: #14 sol. - 4/0 AWG

Current

Operating Voltage 18 VDC

Dimensions

Dimension - Height mm 340.4 mm
Length 16.8 in
Weight 10.10 lb.
Height 13.4 in
Width 2.9 in
Dimensions 16.8 in x 2.9 in x 13.4 in



Force Related

Crimp Force Capacity 6 ton

General

Application - For Use On Overhead Full Tension
Deadends, Full Tension Splices
and Terminals, Stirrups, Splices,
Taps, and Terminals
Trade Name PATRIOT®
Series PATRIOT® Series
Tool Type Battery Actuated Scissor
Action
Container Type Hard Case
Die Type W Die and X Die
UPC 781810673874
Type Crimper and Cutter
UPC 12 Digit 781810673874
UPC 14 Digit GTIN 00781810673874

Logistics

Minimum Pack Quantity 1
Package Contents Tool, BG/D3 Crimp Jaw, (2)
Batteries, Charger, Lanyard,
Hard Case

Operational

Recharge Time 0.5 hr
Battery Type 5.0Ah 18V Li-Ion (Accepts
2.0Ah-6.0Ah Makita LI
Batteries)
Power Source 12V-DC Charger

Product Assets

[Catalog \[English\]](#)