



PATRIOT® Series, 6-Ton Scissor Action, BG/D3 Crimp Jaw, (2) 3.0Ah 18V Li-ion Batteries, 12V-DC Charger, Hard Case

By Burndy
Catalog # [PAT500SJ6LIDC](#)

6T Scissor, BG/D3, 3Ah, DC, HC

Features

- Interchangeable scissor action crimping and cutting jaws available
- 180° Head rotation
- Pistol style body
- Uses W and X dies
- Ergonomically balanced

Application

Crimping and Cutting

Specifications

Standards - RoHS Compliance UI
Status

Conductor

- Crimping Ranges
- Copper: #10 sol. - 500 kcmil
 - Copper Flex: #8 AWG - 350 kcmil
 - Aluminum: #14 sol. - 350 kcmil
 - ACSR: #14 sol. - 4/0 AWG

Current

Operating Voltage 18 VDC

Dimensions

Dimension - Height mm	340.4 mm
Length	16.80 in
Weight	10.10 lb.
Height	13.40 in
Width	2.90 in
Dimensions	16.80 in x 2.90 in x 13.40 in



Force Related

Crimp Force Capacity 6 ton

General

Application - For Use On	Overhead Full Tension Deadends, Full Tension Splices and Terminals, Stirrups, Splices, Taps, and Terminals
Trade Name	PATRIOT®
Series	PATRIOT® Series
Tool Type	Battery Actuated Scissor Action
Container Type	Hard Case
Die Type	W Die and X Die
UPC	781810673836
Type	Crimper and Cutter
UPC 12 Digit	781810673836
UPC 14 Digit GTIN	00781810673836

Logistics

Package Contents Tool, BG/D3 Crimp Jaw, (2) Batteries, Charger, Lanyard, Hard Case

Operational

Recharge Time	0.5 hr
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	12V-DC Charger

Product Assets

[Catalog \[English\]](#)