



6T, ACSR Cut Jaw, Hard Case, 5Ah Makita Batteries

By Burndy
Catalog # [PAT500SJCUTL5](#)

PATRIOT® Series, 6-Ton Scissor Action, ACSR Cutter Jaw, Hard Case, 5.0Ah Makita Batteries

Features

- Interchangeable scissor action crimping and cutting jaws available
- 180° Head rotation
- Pistol style body
- Uses W and X dies
- Ergonomically balanced

Application

Crimping and Cutting

Conductor

Crimping Ranges	• Copper: #10 sol. - 500 kcmil • Copper Flex: #8 AWG - 350 kcmil • Aluminum: #14 sol. - 350 kcmil • ACSR: #14 sol. - 4/0 AWG
-----------------	--

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Weight	10.10 lb.
Height	13.4 in
Width	2.9 in
Length	16.8 in
Dimensions	16.8 in x 2.9 in x 13.4 in

Force Related

Crimp Force Capacity	6 ton
----------------------	-------



General

Tool Type	Battery Actuated Scissor Action
Container Type	Hard Case
Application - For Use On	Overhead Full Tension Deadends, Full Tension Splices and Terminals, Stirrups, Splices, Taps, and Terminals
Die Type	W Die and X Die
UPC	621945470934
Trade Name	PATRIOT®
Type	Crimper and Cutter
UPC 12 Digit	621945470934
Series	PATRIOT® Series

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, ACSR Cut Jaw, (2) Batteries, Charger, Lanyard, Hard Case

Operational

Recharge Time	0.75 hr
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	120V-AC Charger

Product Assets

[Catalog \[English\]](#)