



PATRIOT® 6-Ton Scissor Action, ACSR Cut Jaw, (2) 3.0Ah 18V Li-ion Batteries, 120V-AC Charger, Hard Case

By Burndy
Catalog # [PAT500SJCUTLI](#)

PAT500SJ 6T Scissor Action, ACSR Cut Jaw, 3Ah Li-ion, AC, Hard Case.

Features

- Interchangeable scissor action crimping and cutting jaws available
- 180° Head rotation
- Pistol style body
- Uses W and X dies
- Ergonomically balanced

Application

Crimping and Cutting

General

Application - For Use On	Overhead Full Tension Deadends, Full Tension Splices and Terminals, Stirrups, Splices, Taps, and Terminals
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT500SJCUTLI
Container Type	Hard Case
Crimp Force Capacity	6 ton
Die Type	W Die and X Die
EU RoHS Indicator	Under Review
Power Source	120V-AC Charger
Recharge Time	0.5 h
Tool Type	Battery Actuated Scissor Action
Trade Name	PATRIOT®
Type	Crimper and Cutter
UPC	781810673843
UPC 14 Digit GTIN	00781810673843

Dimensions

Dimension - Height mm	340.4 mm
-----------------------	----------



Dimensions	16.80 in x 2.90 in x 13.40 in
Height	13.4 in
Length	16.8 in
Weight	10.1 lb
Width	2.9 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #10 sol. - 500 kcmil;Copper Flex: #8 AWG - 350 kcmil;Aluminum: #14 sol. - 350 kcmil;ACSR: #14 sol. - 4/0 AWG
-----------------	--

Certifications And Compliance

Standards - RoHS Compliance	UI
Status	

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, ACSR Cut Jaw, (2) Batteries, Charger, Lanyard, Hard Case

Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50024949](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Specifications - PAT500SJCUTLI](#)



A Hubbell brand