



PATRIOT® Series, 6-Ton Latch Head Battery Actuated Crimper, (2) 2.6Ah 18V NiMH Batteries, 120V-AC Charger, Hard Case

By Burndy
Catalog # [PAT60018V](#)

6T Latch Head, NiMH, AC, Hard Case,Discontinuing December 31, 2021

Features

- Specialized latch head design with 180° rotation
- Permanent D3 crimp groove accepts all W Dies
- High speed pump completes crimp in approximately 3 seconds
- Enhanced clearance for tap connections
- Ergonomically balanced

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
EU RoHS Indicator	Yes

Conductor

Crimping Ranges	• Copper: #8 AWG - 600 kcmil • Copper Flex: #8 AWG - 350 kcmil • Aluminum: #8 AWG - 350 kcmil
-----------------	---

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Dimension - Height mm	349.3 mm
-----------------------	----------



Length	14.50 in
Weight	10.9 lb.
Height	13.75 in
Width	3.50 in
Dimensions	14.50 in x 3.50 in x 13.75 in

Force Related

Crimp Force Capacity	6 ton
----------------------	-------

General

Application - For Use On	Copper, Aluminum Terminals and Splices
Trade Name	PATRIOT®
Series	PATRIOT® Series
Tool Type	Battery Actuated Crimper
Container Type	Hard Case
Die Type	W and X Die
UPC	781810361276
Type	Crimper
UPC 12 Digit	781810361276
UPC 14 Digit GTIN	00781810361276

Operational

Recharge Time	0.75 hr
Battery Type	2.6Ah 18V NiMH
Power Source	120V-AC Charger

Product Assets

[Catalog \[English\]](#)