



6T Covered Latch Head Battery Crimper, Pro Bag, 3Ah Makita Batteries

By Burndy
Catalog # [PAT600CLIPB](#)

PATRIOT® Series, 6-Ton Covered Latch Head Battery Crimper, Pro Bag, 3.0Ah Makita Batteries



Features

- Specialized latch head design with 180° rotation
- Permanent D3 crimp groove accepts all W Dies
- High speed pump completes crimp in approximately 3 seconds
- Enhanced clearance for tap connections
- Ergonomically balanced

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Conductor

- Crimping Ranges
- Copper: #8 AWG - 600 kcmil
 - Copper Flex: #8 AWG - 350 kcmil
 - Aluminum: #8 AWG - 350 kcmil

Current

Operating Voltage 18 VDC

Dimensions

Length 14.5 in
Weight 9.00 lb.
Height 13.75 in
Width 3.5 in
Dimensions 14.5 in x 3.5 in x 13.75 in

Force Related

Crimp Force Capacity 6 ton

General

Application - For Use On Copper, Aluminum Terminals and Splices
Trade Name PATRIOT®
Series PATRIOT® Series
Tool Type Battery Actuated Crimper
Container Type Nylon Pro Bag
Die Type W Die and X Die
UPC 621945562233
Type Crimper
UPC 12 Digit 621945562233

Logistics

Minimum Pack Quantity 1
Package Contents Crimper, (2) Batteries, Charger, Lanyard, Nylon Pro Bag
Pallet Quantity 12
Carton Quantity 1

Operational

Recharge Time 0.5 hr
Battery Type 3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source 120V-AC Charger

Product Assets

[Catalog \[English\]](#)