



6T Latch Head Battery Crimper, Hard Case, 5Ah Makita Batteries

By Burndy
Catalog # [PAT600L5](#)

PATRIOT® Series, 6-Ton Latch Head Battery Crimper, Hard Case, 5.0Ah Makita Batteries

Features

- Specialized latch head design with 180° rotation
- Permanent D3 crimp groove accepts all W Dies
- High speed pump completes crimp in approximately 3 seconds
- Enhanced clearance for tap connections
- Ergonomically balanced

Application

Crimping

Specifications

Buy American Compliant	No
EU RoHS Indicator	Under Review

Conductor

Crimping Ranges	• Copper: #8 AWG - 600 kcmil • Copper Flex: #8 AWG - 350 kcmil • Aluminum: #8 AWG - 350 kcmil
-----------------	---

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Length	14.5 in
Weight	8.65 lb.
Height	13.75 in
Width	3.5 in



Dimensions	14.5 in x 3.5 in x 13.75 in
------------	-----------------------------

Force Related

Crimp Force Capacity	6 ton
----------------------	-------

General

Application - For Use On	Copper, Aluminum Terminals and Splices
Trade Name	PATRIOT®
Series	PATRIOT® Series
Tool Type	Battery Actuated Crimper
Container Type	Hard Case
Die Type	W Die and X Die
UPC	621945470958
Type	Crimper
UPC 12 Digit	621945470958

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case

Operational

Recharge Time	0.75 hr
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	120V-AC Charger

Product Assets

[Catalog \[English\]](#)