



6T Latch Head Battery Crimper, Hard Case, 3Ah Makita Batteries

By Burndy
Catalog # [PAT600LI](#)

PATRIOT® Series, 6-Ton Latch Head Battery Crimper, Hard Case, 3.0Ah Makita Batteries

Features

- Specialized latch head design with 180° rotation
- Permanent D3 crimp groove accepts all W Dies
- High speed pump completes crimp in approximately 3 seconds
- Enhanced clearance for tap connections
- Ergonomically balanced

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
Buy American Compliant	No
EU RoHS Indicator	Yes

Conductor

Crimping Ranges	• Copper: #8 AWG - 600 kcmil • Copper Flex: #8 AWG - 350 kcmil • Aluminum: #8 AWG - 350 kcmil
-----------------	---

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Dimension - Height mm	348 mm
Length	14.5 in
Weight	8.65 lb.
Height	3.5 in



Width	13.75 in
Dimensions	14.5 in x 13.75 in x 3.5 in

Force Related

Crimp Force Capacity	6 ton
----------------------	-------

General

Application - For Use On	Copper, Aluminum Terminals and Splices
Trade Name	PATRIOT®
Sub Brand	PATRIOT® CRIMPER
Series	PATRIOT® Series
Tool Type	Battery Actuated Crimper
Container Type	Hard Case
Die Type	W Die and X Die
UPC	781810505328
Type	Crimper
UPC 12 Digit	781810505328
UPC 14 Digit GTIN	00781810505328

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case

Operational

Recharge Time	0.5 hr
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	120V-AC Charger

Product Assets

[Catalog \[English\]](#)