



PATRIOT® Series, 6-Ton Latch Head Battery Crimper, (2) 3.0Ah 18V Li-ion Batteries, 12V-DC Charger, Hard Case

By Burndy
Catalog # [PAT600LIDC](#)

6T Latch Head, 3Ah, DC, Hard Case

Features

- Specialized latch head design with 180° rotation
- Permanent D3 crimp groove accepts all W Dies
- High speed pump completes crimp in approximately 3 seconds
- Enhanced clearance for tap connections
- Ergonomically balanced

Application

Crimping

Specifications

Standards - RoHS Compliance UI
Status

Conductor

- Crimping Ranges
- Copper: #8 AWG - 600 kcmil
 - Copper Flex: #8 AWG - 350 kcmil
 - Aluminum: #8 AWG - 350 kcmil

Dimensions

Dimension - Height mm	0 mm
Length	14.50 in
Weight	8.65 lb.
Height	13.75 in
Width	3.50 in
Dimensions	14.50 in x 3.50 in x 13.75 in



Force Related

Crimp Force Capacity 6 ton

General

Application - For Use On	Copper, Aluminum Terminals and Splices
Trade Name	PATRIOT®
Series	PATRIOT® Series
Tool Type	Battery Actuated Crimper
Container Type	Hard Case
Die Type	W Die and X Die
UPC	781810505373
Type	Crimper
UPC 12 Digit	781810505373
UPC 14 Digit GTIN	00781810505373

Logistics

Package Contents Crimper, (2) Batteries, Charger, Lanyard, Hard Case

Operational

Recharge Time	0.5 hr
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	12V-DC Charger

Product Assets

[Catalog \[English\]](#)