



6T Latch Head Battery Crimper, No Case/Chgr, 3Ah Makita Batteries

By Burndy
Catalog # [PAT600LILCC](#)

PATRIOT® Series, 6-Ton Latch Head Battery Crimper, No Case/Charger, 3.0Ah Makita Batteries



Features

- Specialized latch head design with 180° rotation
- Permanent D3 crimp groove accepts all W Dies
- High speed pump completes crimp in approximately 3 seconds
- Enhanced clearance for tap connections
- Ergonomically balanced

Application

Crimping

Specifications

Standards - RoHS Compliance UI
Status

Conductor

- Crimping Ranges
- Copper: #8 AWG - 600 kcmil
 - Copper Flex: #8 AWG - 350 kcmil
 - Aluminum: #8 AWG - 350 kcmil

Dimensions

Dimension - Height mm	0 mm
Length	14.5 in
Weight	8.65 lb.
Height	13.75 in
Width	3.5 in
Dimensions	14.5 in x 3.5 in x 13.75 in

Force Related

Crimp Force Capacity 6 ton

General

Application - For Use On	Copper, Aluminum Terminals and Splices
Trade Name	PATRIOT®
Series	PATRIOT® Series
Tool Type	Battery Actuated Crimper
Container Type	No Case/Bag
Die Type	W Die and X Die
UPC	781810650974
Type	Crimper
UPC 12 Digit	781810650974
UPC 14 Digit GTIN	00781810650974

Logistics

Minimum Pack Quantity 1
Package Contents Crimper, (2) Batteries, Lanyard

Operational

Recharge Time 0.5 hr
Battery Type 3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)

Power Source No Charger

Product Assets

[Catalog \[English\]](#)