



11T Dieless Latch Head Battery Crimper,
Hard Case, 3Ah Makita Batteries

By Burndy
Catalog # [PAT644LI](#)

PATRIOT® Series, 11-Ton Dieless Latch Head Battery Crimper, Hard Case, 3.0Ah Makita Batteries

Features

- Dieless System with range taking capability
- #4 AWG -1000 kcmil Copper and Aluminum,#4 AWG - 556.5 kcmil ACSR, AAC, AAAC, ACAR
- 355° Rotatable latch head
- Audible pop-off indicates properly completed crimps
- Ergonomically balanced

Application

Crimping

Specifications

Standards - RoHS Compliance Status	EX
Buy American Compliant	No
EU RoHS Indicator	Yes

Conductor

Crimping Ranges	• Copper: #4 AWG - 1000 kcmil • Copper Flex: #2 AWG - 777 kcmil • Aluminum: #6 AWG - 900 kcmil • ACSR #4 AWG - 556.5 kcmil
-----------------	--

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Dimension - Height mm	349.3 mm
Length	15.6 in
Weight	14.55 lb.
Height	14.1 in

Width	3.2 in
Dimensions	15.6 in x 3.2 in x 14.1 in

Force Related

Crimp Force Capacity	11 ton
----------------------	--------

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Trade Name	PATRIOT®
Sub Brand	PATRIOT® CRIMPER
Series	PATRIOT® Series
Tool Type	Battery Actuated Crimper
Container Type	Hard Case
Die Type	Dieless
UPC	781810505489
Type	Crimper
UPC 12 Digit	781810505489
UPC 14 Digit GTIN	00781810505489

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case

Operational

Recharge Time	0.5 hr
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	120V-AC Charger

Product Assets

[Catalog \[English\]](#)