



PATRIOT® 11-Ton Dieless Latch Head Battery Actuated Crimper, Hydraulic Self-Contained, Hard Case, No Batteries or Charger

By Burndy
Catalog # [PAT644LILCB](#)



PAT644 11T Dieless Latch Head Battery Crimper, Hard Case, No Batteries or Charger.

Features

- Dieless System with range taking capability
- #4 AWG -1000 kcmil Copper and Aluminum,#4 AWG - 556.5 kcmil ACSR, AAC, AAAC, ACAR
- 355° Rotatable latch head
- Audible pop-off indicates properly completed crimps
- Ergonomically balanced

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT644LILCB
Container Type	Hard Case
Crimp Force Capacity	12 ton
Die Type	Dieless
Power Source	No Charger
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	781810540886
UPC 14 Digit GTIN	00781810540886

Dimensions

Dimension - Height mm	0 mm
Dimensions	15.62 in x 3.25 in x 14.12 in
Height	14.12 in
Length	15.62 in
Weight	14.55 lb
Width	3.25 in

Conductor Related

Crimping Ranges	Copper: #4 AWG - 1000 kcmil; Copper Flex: #2 AWG - 777 kcmil; Aluminum: #6 AWG - 900 kcmil; ACSR #4 AWG - 556.5 kcmil
-----------------	---

Certifications And Compliance

Standards - RoHS Compliance Status	EX
---------------------------------------	----

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, Lanyard, Hard Case

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Specifications - PAT644LILCB](#)



A Hubbell brand