



11T Dieless Latch Head Battery Crimper, Pro Bag, 3Ah Makita Batteries

By Burndy
Catalog # [PAT644LIPB](#)

PATRIOT® Series, 11-Ton Dieless Latch Head Battery Crimper, Pro Bag, 3.0Ah Makita Batteries



Features

- Dieless System with range taking capability
- #4 AWG -1000 kcmil Copper and Aluminum,#4 AWG - 556.5 kcmil ACSR, AAC, AAAC, ACAR
- 355° Rotatable latch head
- Audible pop-off indicates properly completed crimps
- Ergonomically balanced

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
Buy American Compliant	No
EU RoHS Indicator	Yes

Conductor

Crimping Ranges	• Copper: #4 AWG - 1000 kcmil • Copper Flex: #2 AWG - 777 kcmil • Aluminum: #6 AWG - 900 kcmil • ACSR #4 AWG - 556.5 kcmil
-----------------	--

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Length	15.62 in
Weight	14.55 lb.
Height	14.12 in
Width	3.25 in

Dimensions	15.62 in x 3.25 in x 14.12 in
------------	-------------------------------

Force Related

Crimp Force Capacity	11 ton
----------------------	--------

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Trade Name	PATRIOT®
Series	PATRIOT® Series
Tool Type	Battery Actuated Crimper
Container Type	Nylon Pro Bag
Die Type	Dieless
UPC	621945561748
Type	Crimper
UPC 12 Digit	621945561748

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Nylon Pro Bag
Pallet Quantity	12
Carton Quantity	1

Operational

Recharge Time	0.5 hr
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	120V-AC Charger

Product Assets

[Catalog \[English\]](#)