



12T Covered C-Head Battery Crimper, Hard Case, 5Ah Makita Batteries

By Burndy
Catalog # [PAT750CL5](#)

12T Covered C-Head, 5Ah, AC, Hard Case



Features

- C-Head with 1.65" jaw opening
- 355° head rotation
- Uses U dies
- Ergonomic design and overmolded handle for comfort grip
- Patented T-Track alignment guide for HYGROUND® as well as other asymmetrical connectors
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

Application

Crimping

Specifications

EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Conductor

- | | |
|-----------------|--|
| Crimping Ranges | <ul style="list-style-type: none">• Copper: #14 sol. - 750 kcmil• Aluminum: #8 sol. - 750 kcmil• ACSR: #4 AWG - 556.5 kcmil• Ground Rod: 1/2" - 1" diameter |
|-----------------|--|

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Length	15.75 in
Weight	15.20 lb.
Height	13.5 in
Width	3.5 in
Jaw Width	1.65 in

Dimensions	15.75 in x 3.5 in x 13.5 in
------------	-----------------------------

Force Related

Crimp Force Capacity	12 ton
----------------------	--------

General

Application - For Use On	Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Trade Name	PATRIOT®
Series	PATRIOT® Series
Tool Type	Battery Actuated Crimper
Container Type	Hard Case
Die Type	U Die
UPC	621945477476
Type	Crimper
UPC 12 Digit	621945477476

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case

Operational

Recharge Time	0.75 hr
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	120V-AC Charger

Product Assets

[Catalog \[English\]](#)