



PATRIOT® Series, 12-Ton Covered C-Head Battery Crimper, Hydraulic Self-Contained, (2) 5.0Ah 18V Li-ion Batteries, 12V-DC Charger, Hard Case

By Burndy
Catalog # PAT750CL5DC

12T Covered C-Head, 5Ah, DC, Hard Case

Features

- C-Head with 1.65" jaw opening
- 355° head rotation
- Uses U dies
- Ergonomic design and overmolded handle for comfort grip
- Patented T-Track alignment guide for HYGROUND® as well as other asymmetrical connectors
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

Application

Crimping

Conductor

Crimping Ranges	• Copper: #14 sol. - 750 kcmil • Aluminum: #8 sol. - 750 kcmil • ACSR: #4 AWG - 556.5 kcmil • Ground Rod: 1/2" - 1" diameter
-----------------	--

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Weight	15.20 lb.
Height	13.50 in
Width	3.5 in
Length	15.75 in
Jaw Width	1.65 in
Dimensions	15.75 in x 3.5 in x 13.50 in



Force Related

Crimp Force Capacity	12 ton
----------------------	--------

General

Tool Type	Battery Actuated Crimper
Container Type	Hard Case
Application - For Use On	Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Die Type	U Die
UPC	621945477490
Trade Name	PATRIOT®
Type	Crimper
UPC 12 Digit Series	621945477490 PATRIOT® Series

Logistics

Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case
------------------	---

Operational

Recharge Time	0.75 hr
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	12V-DC Charger

Product Assets

[Catalog \[English\]](#)