



12T C-Head Battery Crimper, Pro Bag, 5Ah Makita Batteries

By Burndy
Catalog # [PAT750L5PB](#)

PATRIOT® Series, 12-Ton C-Head Battery Crimper, Pro Bag, 5.0Ah Makita Batteries



Features

- C-Head with 1.65" jaw opening
- 355° head rotation
- Uses U dies
- Ergonomic design and overmolded handle for comfort grip
- Patented T-Track alignment guide for HYGROUND® as well as other asymmetrical connectors
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

Application

Crimping

Specifications

Buy American Compliant	No
EU RoHS Indicator	Under Review
UL Listed	No

Conductor

Crimping Ranges	• Copper: #14 sol. - 750 kcmil • Aluminum: #8 sol. - 750 kcmil • ACSR: #4 AWG - 556.5 kcmil • Ground Rod: 1/2" - 1" diameter
-----------------	--

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Length	15.75 in
Weight	14.25 lb.
Height	13.5 in
Width	3.5 in
Jaw Width	1.65 in
Dimensions	15.75 in x 3.5 in x 13.5 in

Force Related

Crimp Force Capacity	12 ton
----------------------	--------

General

Application - For Use On	Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Trade Name	PATRIOT®
Sub Brand	PATRIOT® Crimper
Series	PATRIOT® Series
Tool Type	Battery Actuated Crimper
Container Type	Nylon Pro Bag
Die Type	U Die
UPC	621945561427
Type	Crimper
UPC 12 Digit	621945561427

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Nylon Pro Bag
Pallet Quantity	12
Carton Quantity	1

Operational

Recharge Time	0.75 hr
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	120V-AC Charger

Product Assets

[Catalog \[English\]](#)