



PATRIOT® Series, 12-Ton C-Head Battery Crimper, Hydraulic Self-Contained, (2) 3.0Ah 18V Li-ion Batteries, 12V-DC Charger, Hard Case

By Burndy
Catalog # PAT750LIDC

12T C-Head, 3Ah, DC, Hard Case

Features

- C-Head with 1.65" jaw opening
- 355° head rotation
- Uses U dies
- Ergonomic design and overmolded handle for comfort grip
- Patented T-Track alignment guide for HYGROUND® as well as other asymmetrical connectors
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Conductor

- Crimping Ranges
- Copper: #14 sol. - 750 kcmil
 - Aluminum: #8 sol. - 750 kcmil
 - ACSR: #4 AWG - 556.5 kcmil
 - Ground Rod: 1/2" - 1" diameter

Current

Operating Voltage 18 VDC

Dimensions

Dimension - Height mm 342.9 mm
Length 15.75 in
Weight 14.25 lb.
Height 13.50 in
Width 3.50 in



Jaw Width 1.65 in
Dimensions 15.75 in x 3.50 in x 13.50 in

Force Related

Crimp Force Capacity 12 ton

General

Application - For Use On Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding

Trade Name PATRIOT®
Series PATRIOT® Series
Tool Type Battery Actuated Crimper
Container Type Hard Case
Die Type U Die
UPC 781810505199
Type Crimper
UPC 12 Digit 781810505199
UPC 14 Digit GTIN 00781810505199

Logistics

Package Contents Crimper, (2) Batteries, Charger, Lanyard, Hard Case

Operational

Recharge Time 0.5 hr
Battery Type 3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)

Power Source 12V-DC Charger

Product Assets

[Catalog \[English\]](#)