



PATRIOT® Series, 12-Ton C-Head Battery Crimper, Hydraulic Self-Contained, No Batteries, No Charger, No Case

By Burndy
Catalog # PAT750LILCCB

12T C-Head, No B/C/C

Features

- C-Head with 1.65" jaw opening
- 355° head rotation
- Uses U dies
- Ergonomic design and overmolded handle for comfort grip
- Patented T-Track alignment guide for HYGROUND® as well as other asymmetrical connectors
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Conductor

- Crimping Ranges
- Copper: #14 sol. - 750 kcmil
 - Aluminum: #8 sol. - 750 kcmil
 - ACSR: #4 AWG - 556.5 kcmil
 - Ground Rod: 1/2" - 1" diameter

Current

Operating Voltage 18 VDC

Dimensions

Dimension - Height mm 0 mm
Length 15.75 in
Weight 14.25 lb.
Height 13.50 in
Width 3.50 in



Jaw Width 1.65 in
Dimensions 15.75 in x 3.50 in x 13.50 in

Force Related

Crimp Force Capacity 12 ton

General

Application - For Use On Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding

Trade Name PATRIOT®
Series PATRIOT® Series
Tool Type Battery Actuated Crimper
Container Type No Case/Bag
Die Type U Die
UPC 781810566107
Type Crimper
UPC 12 Digit 781810566107
UPC 14 Digit GTIN 00781810566107

Logistics

Package Contents Crimper, Lanyard
Carton Quantity 1

Operational

Battery Type No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)

Power Source No Charger

Product Assets

[Catalog \[English\]](#)