



PATRIOT® T3 Technology 12-Ton Battery Crimper, C-Head, Rubber Covered, (2) 3.0Ah 18V Li-Ion Batteries, 120V-AC Charger, Hard Case

By Burndy
Catalog # [PAT750T3C03A2](#)

PAT750T3 Tech 12T Battery Crimper, C-Head, Rubber Covered, 3Ah Li-Ion, AC, Hard Case.

Features

- TRACK crimp locations with onboard GPS - BURNDY Exclusive!
- TRACE individual crimps with comments and output force validation
- TRANSMIT via Bluetooth® technology and sync data to the cloud
- C-head with 1.65" jaw opening with 355° head rotation
- Used with U dies
- Bright LED worklight and Red/Green LED to validate output force
- Improved ergonomic design with more balance and better grip to reduce user fatigue
- Patented T-Track alignment guide for HYGROUND® as well as other asymmetrical connectors
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

Application

Crimping

General

Application - For Use On	Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT750T3C03A2
Container Type	Hard Case
Crimp Force Capacity	12 ton
Die Type	U Die
Power Source	120V-AC Charger
Recharge Time	0.5 h
Tool Type	Battery Actuated Crimper, T3 Technology
Trade Name	PATRIOT®



Type	Crimper
UPC	621945558960

Dimensions

Dimensions	15.75 in x 3.25 in x 14.75 in
Height	14.75 in
Jaw Width	1.65 in
Length	15.75 in
Weight	15.8 lb
Width	3.25 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #14 sol. - 750 kcmil; Aluminum: #8 sol. - 750 kcmil; ACSR: #4 AWG - 556.5 kcmil; Ground Rod: 1/2" - 1" diameter
-----------------	--

Logistics

Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case
------------------	---

Product Assets

[Brochures - T3 Technology Trifold Brochure](#)
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50106314](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Specifications - PAT750T3C03A2](#)
[Video - BURNDY T3 APP Features and Benefits](#)
[Video - BURNDY T3 Is Here - PAT750T3](#)
[Video - BURNDY T3 APP Install & Register](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-PAT750T3C03A2-SPEC-EN | REV 7/2025