



PATRIOT® Series, T3 Technology 12-Ton Battery Crimper, C-Head, Rubber Covered, (2) 3.0Ah 18V Li-Ion Batteries, 12V-DC Charger, Hard Case

By Burndy
Catalog # PAT750T3C03D2

T3 Tech 12T Cvrdr C-Head, 3Ah, DC, HC

Features

- TRACK crimp locations with onboard GPS - BURNDY Exclusive!
- TRACE individual crimps with comments and output force validation
- TRANSMIT via Bluetooth® technology and sync data to the cloud
- C-head with 1.65" jaw opening with 355° head rotation
- Used with U dies
- Bright LED worklight and Red/Green LED to validate output force
- Improved ergonomic design with more balance and better grip to reduce user fatigue
- Patented T-Track alignment guide for HYGROUND® as well as other asymmetrical connectors
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

Application

Crimping

Conductor

- Crimping Ranges
- Copper: #14 sol. - 750 kcmil
 - Aluminum: #8 sol. - 750 kcmil
 - ACSR: #4 AWG - 556.5 kcmil
 - Ground Rod: 1/2" - 1" diameter

Current

Operating Voltage18 VDC

Dimensions

Weight15.80 lb.
Height14.75 in
Width3.25 in



Length15.75 in
Jaw Width1.65 in
Dimensions15.75 in x 3.25 in x 14.75 in

Force Related

Crimp Force Capacity12 ton

General

Tool TypeBattery Actuated Crimper, T3 Technology
Container TypeHard Case
Application - For Use OnTension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Die TypeU Die
UPC621945558977
Trade NamePATRIOT®
TypeCrimper
UPC 12 Digit621945558977
SeriesPATRIOT® Series

Logistics

Package ContentsCrimper, (2) Batteries, Charger, Lanyard, Hard Case

Operational

Recharge Time0.5 hr
Battery Type3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source12V-DC Charger

Product Assets

[Catalog \[English\]](#)