



PATRIOT® Series, T3 Technology 12-Ton Battery Crimper, C-Head, Rubber Covered, (2) 3.0Ah 18V Li-Ion Batteries, 12V-DC Charger, Nylon Pro Bag

By Burndy
Catalog # PAT750T3C03D3

T3 Tech 12T Cvrdr C-Head, 3Ah, DC, PB

Features

- TRACK crimp locations with onboard GPS - BURNDY Exclusive!
- TRACE individual crimps with comments and output force validation
- TRANSMIT via Bluetooth® technology and sync data to the cloud
- C-head with 1.65" jaw opening with 355° head rotation
- Used with U dies
- Bright LED worklight and Red/Green LED to validate output force
- Improved ergonomic design with more balance and better grip to reduce user fatigue
- Patented T-Track alignment guide for HYGROUND® as well as other asymmetrical connectors
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

Application

Crimping

Specifications

EU RoHS Indicator Contact Manufacturer

Conductor

- Crimping Ranges
- Copper: #14 sol. - 750 kcmil
 - Aluminum: #8 sol. - 750 kcmil
 - ACSR: #4 AWG - 556.5 kcmil
 - Ground Rod: 1/2" - 1" diameter

Current

Operating Voltage 18 VDC

Dimensions

Length 15.75 in
Weight 15.80 lb.



Height 14.75 in
Width 3.25 in
Jaw Width 1.65 in
Dimensions 15.75 in x 3.25 in x 14.75 in

Force Related

Crimp Force Capacity 12 ton

General

Application - For Use On Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Trade Name PATRIOT®
Series PATRIOT® Series
Tool Type Battery Actuated Crimper, T3 Technology
Container Type Nylon Pro Bag
Die Type U Die
UPC 621945561342
Type Crimper
UPC 12 Digit 621945561342

Logistics

Package Contents Crimper, (2) Batteries, Charger, Lanyard, Nylon Pro Bag
Pallet Quantity 12
Carton Quantity 1

Operational

Recharge Time 0.5 hr
Battery Type 3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source 12V-DC Charger

Product Assets

[Catalog \[English\]](#)