



# T3 Tech 12T Battery Crimper, C-Head, No Case/Batt/Chgr, Makita Power

By Burndy  
Catalog # [PAT750T3U0000](#)

PATRIOT® Series, T3 Technology 12-Ton Battery Crimper, C-Head, No Batteries, Makita Power

## Features

- TRACK crimp locations with onboard GPS - BURNDY Exclusive!
- TRACE individual crimps with comments and output force validation
- TRANSMIT via Bluetooth® technology and sync data to the cloud
- C-head with 1.65" jaw opening with 355° head rotation
- Used with U dies
- Bright LED worklight and Red/Green LED to validate output force
- Improved ergonomic design with more balance and better grip to reduce user fatigue
- Patented T-Track alignment guide for HYGROUND® as well as other asymmetrical connectors
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

## Application

Crimping

## Conductor

|                 |                                                                                                                                                                                                      |
|-----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Crimping Ranges | <ul style="list-style-type: none"><li>• Copper: #14 sol. - 750 kcmil</li><li>• Aluminum: #8 sol. - 750 kcmil</li><li>• ACSR: #4 AWG - 556.5 kcmil</li><li>• Ground Rod: 1/2" - 1" diameter</li></ul> |
|-----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

## Current

|                   |        |
|-------------------|--------|
| Operating Voltage | 18 VDC |
|-------------------|--------|

## Dimensions

|        |           |
|--------|-----------|
| Weight | 14.85 lb. |
| Height | 14.75 in  |



|            |                               |
|------------|-------------------------------|
| Width      | 3.25 in                       |
| Length     | 15.75 in                      |
| Jaw Width  | 1.65 in                       |
| Dimensions | 15.75 in x 3.25 in x 14.75 in |

## Force Related

|                      |        |
|----------------------|--------|
| Crimp Force Capacity | 12 ton |
|----------------------|--------|

## General

|                          |                                                                                           |
|--------------------------|-------------------------------------------------------------------------------------------|
| Tool Type                | Battery Actuated Crimper, T3 Technology                                                   |
| Container Type           | No Case/Bag                                                                               |
| Application - For Use On | Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding |
| Die Type                 | U Die                                                                                     |
| UPC                      | 621945559585                                                                              |
| Trade Name               | PATRIOT®                                                                                  |
| Type                     | Crimper                                                                                   |
| UPC 12 Digit             | 621945559585                                                                              |
| Series                   | PATRIOT® Series                                                                           |

## Logistics

|                  |                  |
|------------------|------------------|
| Package Contents | Crimper, Lanyard |
|------------------|------------------|

## Operational

|              |                                                                 |
|--------------|-----------------------------------------------------------------|
| Battery Type | No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries) |
| Power Source | No Charger                                                      |

## Product Assets

[Catalog \[English\]](#)