



4-POINT 6T Dieless Battery Crimper, Guides, Hard Case, No Batt/Chgr Makita Power

By Burndy
Catalog # [PAT81K2U0002](#)

PATRIOT® 4-POINT® Series, 6-Ton Dieless Latch Head Battery Crimper, Guides, Hard Case, No Batteries, Makita Power

Features

- Dieless System with range taking capabilities
- 360° head rotation
- Unique crimping guides for improved reliability and ease of use
- Mechanical ram release (no battery consumption)
- Overmolded handle for comfort and improved grip
- Ergonomically balanced

Application

Crimping

Specifications

Buy American Compliant No

Conductor

- Crimping Ranges
- Copper: #8 AWG -1000 kcmil
 - Copper Flex: #8 AWG - 777.7 kcmil
 - Aluminum: #8 AWG - 750 kcmil

Current

Operating Voltage 18 VDC

Dimensions

Weight 11.05 lb.
Height 14.93 in
Width 3.25 in



Length 15.2 in
Dimensions 15.2 in x 3.25 in x 14.93 in

Force Related

Crimp Force Capacity 6 ton

General

Tool Type Battery Actuated Crimper
Container Type Hard Case
Application - For Use On Copper, Aluminum Terminals and Splices, HYPLUG™
Die Type Dieless
UPC 621945645370
Trade Name PATRIOT® 4-POINT®
Type Crimper
UPC 12 Digit 621945645370
Series PATRIOT® 4-POINT® Series

Logistics

Package Contents Crimper, Lanyard, Hard Case

Operational

Battery Type No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source No Charger

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)