



PATRIOT® 4-POINT® Series, 6-Ton Dieless Latch Head Battery Crimper, Guides, (2) 3.0Ah 18V Li-ion Batteries, 12V-DC Charger, Hard Case

By Burndy
Catalog # PAT81K2U03D2

6T 4PT Latch, Guides, 3Ah, DC, HC

Features

- Dieless System with range taking capabilities
- 360° head rotation
- Unique crimping guides for improved reliability and ease of use
- Mechanical ram release (no battery consumption)
- Overmolded handle for comfort and improved grip
- Ergonomically balanced

Application

Crimping

Conductor

- Crimping Ranges
- Copper: #8 AWG -1000 kcmil
 - Copper Flex: #8 AWG - 777.7 kcmil
 - Aluminum: #8 AWG - 750 kcmil

Dimensions

Weight	11.05 lb.
Height	14.93 in
Width	3.25 in
Length	15.2 in
Dimensions	15.2 in x 3.25 in x 14.93 in



General

Tool Type	Battery Actuated Crimper
Container Type	Hard Case
Application - For Use On	Copper, Aluminum Terminals and Splices, HYPLUG™
Die Type	Dieless
UPC	621945645448
Trade Name	PATRIOT® 4-POINT®
Type	Crimper
UPC 12 Digit	621945645448
Series	PATRIOT® 4-POINT® Series

Logistics

Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case
------------------	---

Operational

Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	12V-DC Charger

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)