



PATRIOT® 4-POINT® 6-Ton Dieless Latch Head Battery Crimper, Guides, (2) 5.0Ah 18V Li-ion Batteries, 120V-AC Charger, Pro Bag

By Burndy
Catalog # [PAT81K2U05A3](#)



PAT81K2 4-POINT® 6T Dieless Latch Head Battery Crimper, Guides, 5Ah Li-ion, AC, Pro Bag

Features

- Dieless System with range taking capabilities
- 360° head rotation
- Unique crimping guides for improved reliability and ease of use
- Mechanical ram release (no battery consumption)
- Overmolded handle for comfort and improved grip
- Ergonomically balanced

Application

Crimping

General

Application - For Use On	Copper, Aluminum Terminals and Splices, HYPLUG™
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT81K2U05A3
Container Type	Nylon Pro Bag
Crimp Force Capacity	6 ton
Die Type	Dieless
Power Source	120V-AC Charger
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT® 4-POINT®
Type	Crimper
UPC	621945645431

Dimensions

Dimensions	15.2 in x 3.25 in x 14.93 in
------------	------------------------------

Height	14.93 in
Length	15.2 in
Weight	11.05 lb
Width	3.25 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #8 AWG -1000 kcmil; Copper Flex: #8 AWG - 777.7 kcmil; Aluminum: #8 AWG - 750 kcmil
-----------------	---

Logistics

Carton Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Nylon Pro Bag
Pallet Quantity	12

Product Assets

- [Brochures - PAT81K2 Series Brochure](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Safety Operating & Maintenance](#)
[Instructions - PATRIOT PAT81K@ Series Crimp Tools](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50123580](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Specifications - PAT81K2U05A3](#)
[Video - PATRIOT® 4-POINT® PAT81K2](#)