



PAT81KFTLI

By Burndy
Catalog # PAT81KFTLI

Discontinued - Suggest PAT81K2U03A2



Features

- Dieless System with range taking capabilities
- 360° head rotation
- Mechanical ram release (no battery consumption)
- Overmolded handle for comfort and improved grip
- Ergonomically balanced

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
EU RoHS Indicator	Yes

Conductor

Crimping Ranges	• Copper: #8 AWG -1000 kcmil • Copper Flex: #8 AWG - 777.7 kcmil • Aluminum: #8 AWG - 750 kcmil
-----------------	---

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Dimension - Height mm	358.1 mm
Length	15.62 in

Weight	13.2 lb.
Height	14.12 in
Width	3.25 in
Dimensions	15.62 in x 3.25 in x 14.12 in

Force Related

Crimp Force Capacity	6 ton
----------------------	-------

General

Application - For Use On	Copper, Aluminum Terminals and Splices, HYPLUG™
Trade Name	PATRIOT® 4-POINT®
Tool Type	Battery Actuated Crimper
Container Type	Hard Case
Die Type	Dieless
UPC	781810505380
Type	Crimper
UPC 12 Digit	781810505380
UPC 14 Digit GTIN	00781810505380

Operational

Recharge Time	0.5 hr
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	120V-AC Charger

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)