



129 Series Latch Head Battery Cutter, Hard Case, 3Ah Makita Batteries

By Burndy
Catalog # [PATCUT129LI](#)

7T Latch Cut, ACSR, 3Ah, AC, HC

Features

- Special latch head design provides interference free closure for mid-span cuts
- 180° Head rotation
- Overmolded handle and ergonomic design
- One-handed operation for advance, retract and hold

Application

Cutting

Specifications

Standards - RoHS Compliance Status	EX
Buy American Compliant	No
EU RoHS Indicator	Yes

Conductor

Crimping Ranges	• Cutting Capacity: Copper/Aluminum up to 1.29" • ACSR up to 1113 kcmil • Ground Rod up to 5/8" • Rebar up to 1/2" • Soft Steel Bolts up to 5/8" • Standard Guy up to 1/2" • EHS Guy Strand up to 3/8"
-----------------	--

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Dimension - Height mm	0 mm
Length	14.5 in
Weight	9.85 lb.
Height	13.5 in
Width	3.5 in

Dimensions	14.5 in x 3.5 in x 13.5 in
------------	----------------------------

Force Related

Crimp Force Capacity	7 ton
----------------------	-------

General

Application - For Use On	• ACSR, Aluminum, Copper Cable • Ground Rod • Rebar • Soft Steel Bolts • Standard Guy • EHS Guy Strand
Trade Name	PATRIOT®
Sub Brand	PATRIOT® CUTTER
Series	PATRIOT® Series
Tool Type	Battery Actuated Cutter
Container Type	Hard Case
UPC	781810505212
Type	Cutter
UPC 12 Digit	781810505212
UPC 14 Digit GTIN	00781810505212

Logistics

Minimum Pack Quantity	1
Package Contents	Cutter, (2) Batteries, Charger, Lanyard, Hard Case

Operational

Recharge Time	0.5 hr
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	120V-AC Charger

Product Assets

[Catalog \[English\]](#)