



PATRIOT® Series, 129 Series Latch Head
Battery Cutter, (2) 3.0Ah 18V Li-ion
Batteries, 12V-DC Charger, Hard Case

By Burndy
Catalog # [PATCUT129LIDC](#)

7T Latch Cut, ACSR, 3Ah, DC, HC

Features

- Special latch head design provides interference free closure for mid-span cuts
- 180° Head rotation
- Overmolded handle and ergonomic design
- One-handed operation for advance, retract and hold

Application

Cutting

Specifications

Standards - RoHS Compliance EX
Status

Conductor

- Crimping Ranges
- Cutting Capacity:
Copper/Aluminum up to
1.29"
 - ACSR up to 1113 kcmil
 - Ground Rod up to 5/8"
 - Rebar up to 1/2"
 - Soft Steel Bolts up to 5/8"
 - Standard Guy up to 1/2"
 - EHS Guy Strand up to 3/8"

Current

Operating Voltage 18 VDC

Dimensions

Dimension - Height mm	0 mm
Length	14.50 in
Weight	9.85 lb.
Height	13.50 in
Width	3.50 in



Dimensions 14.50 in x 3.50 in x 13.50 in

Force Related

Crimp Force Capacity 7 ton

General

- Application - For Use On
- ACSR, Aluminum, Copper
Cable
 - Ground Rod
 - Rebar
 - Soft Steel Bolts
 - Standard Guy
 - EHS Guy Strand

Trade Name	PATRIOT®
Series	PATRIOT® Series
Tool Type	Battery Actuated Cutter
Container Type	Hard Case
UPC	781810505236
Type	Cutter
UPC 12 Digit	781810505236
UPC 14 Digit GTIN	00781810505236

Logistics

Package Contents Cutter, (2) Batteries, Charger,
Lanyard, Hard Case

Operational

Recharge Time	0.5 hr
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	12V-DC Charger

Product Assets

[Catalog \[English\]](#)