



129 Series Latch Head Battery Cutter, Hard Case, No Batt/Chgr, Makita Power

By Burndy
Catalog # [PATCUT129LILCB](#)

PATRIOT® Series, 129 Series Latch Head Battery Cutter, Hard Case, No Batteries, Makita Power

Features

- Special latch head design provides interference free closure for mid-span cuts
- 180° Head rotation
- Overmolded handle and ergonomic design
- One-handed operation for advance, retract and hold

Application

Cutting

Specifications

Standards - RoHS Compliance EX
Status

Conductor

- | | |
|-----------------|--|
| Crimping Ranges | <ul style="list-style-type: none">• Cutting Capacity: Copper/Aluminum up to 1.29"• ACSR up to 1113 kcmil• Ground Rod up to 5/8"• Rebar up to 1/2"• Soft Steel Bolts up to 5/8"• Standard Guy up to 1/2"• EHS Guy Strand up to 3/8" |
|-----------------|--|

Dimensions

Dimension - Height mm	0 mm
Length	14.5 in
Weight	9.85 lb.
Height	13.5 in
Width	3.5 in
Dimensions	14.5 in x 3.5 in x 13.5 in

Force Related

Crimp Force Capacity	7 ton
----------------------	-------

General

Application - For Use On	• ACSR, Aluminum, Copper Cable • Ground Rod • Rebar • Soft Steel Bolts • Standard Guy • EHS Guy Strand
Trade Name	PATRIOT®
Series	PATRIOT® Series
Tool Type	Battery Actuated Cutter
Container Type	Hard Case
UPC	781810540909
Type	Cutter
UPC 12 Digit	781810540909
UPC 14 Digit GTIN	00781810540909

Logistics

Minimum Pack Quantity	1
Package Contents	Cutter, Lanyard, Hard Case

Operational

Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	No Charger

Product Assets

[Catalog \[English\]](#)