



129 Series Latch Head Battery Cutter, Pro Bag, No Batt/Chgr, Makita Power

By Burndy
Catalog # [PATCUT129LILCBPB](#)

PATRIOT® Series, 129 Series Latch Head Battery Cutter, Pro Bag, No Batteries, Makita Power

Features

- Special latch head design provides interference free closure for mid-span cuts
- 180° Head rotation
- Overmolded handle and ergonomic design
- One-handed operation for advance, retract and hold

Application

Cutting

Specifications

Standards - RoHS Compliance EX
Status

Conductor

- | | |
|-----------------|--|
| Crimping Ranges | <ul style="list-style-type: none">• Cutting Capacity: Copper/Aluminum up to 1.29"• ACSR up to 1113 kcmil• Ground Rod up to 5/8"• Rebar up to 1/2"• Soft Steel Bolts up to 5/8"• Standard Guy up to 1/2"• EHS Guy Strand up to 3/8" |
|-----------------|--|

Current

Operating Voltage 18 VDC

Dimensions

Length	14.5 in
Weight	9.85 lb.
Height	13.5 in
Width	3.5 in
Dimensions	14.5 in x 3.5 in x 13.5 in



Force Related

Crimp Force Capacity 7 ton

General

- | | |
|--------------------------|--|
| Application - For Use On | <ul style="list-style-type: none">• ACSR, Aluminum, Copper Cable• Ground Rod• Rebar• Soft Steel Bolts• Standard Guy• EHS Guy Strand |
|--------------------------|--|

Trade Name	PATRIOT®
Series	PATRIOT® Series
Tool Type	Battery Actuated Cutter
Container Type	Nylon Pro Bag
UPC	621945561533
Type	Cutter
UPC 12 Digit	621945561533

Logistics

Minimum Pack Quantity	1
Package Contents	Cutter, Lanyard, Nylon Pro Bag
Pallet Quantity	12
Carton Quantity	1

Operational

Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	No Charger

Product Assets

[Catalog \[English\]](#)