



129 Series Latch Head Battery Cutter, Pro Bag, 3Ah Makita Batteries

By Burndy
Catalog # [PATCUT129LIPB](#)

PATRIOT® Series, 129 Series Latch Head Battery Cutter, Pro Bag, 3.0Ah Makita Batteries

Features

- Special latch head design provides interference free closure for mid-span cuts
- 180° Head rotation
- Overmolded handle and ergonomic design
- One-handed operation for advance, retract and hold

Application

Cutting

Specifications

Standards - RoHS Compliance Status	EX
Buy American Compliant	No
EU RoHS Indicator	Yes

Conductor

Crimping Ranges	• Cutting Capacity: Copper/Aluminum up to 1.29" • ACSR up to 1113 kcmil • Ground Rod up to 5/8" • Rebar up to 1/2" • Soft Steel Bolts up to 5/8" • Standard Guy up to 1/2" • EHS Guy Strand up to 3/8"
-----------------	--

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Length	14.5 in
Weight	9.85 lb.
Height	13.5 in
Width	3.5 in
Dimensions	14.5 in x 3.5 in x 13.5 in



Force Related

Crimp Force Capacity	7 ton
----------------------	-------

General

Application - For Use On	• ACSR, Aluminum, Copper Cable • Ground Rod • Rebar • Soft Steel Bolts • Standard Guy • EHS Guy Strand
Trade Name	PATRIOT®
Series	PATRIOT® Series
Tool Type	Battery Actuated Cutter
Container Type	Nylon Pro Bag
UPC	621945561977
Type	Cutter
UPC 12 Digit	621945561977

Logistics

Minimum Pack Quantity	1
Package Contents	Cutter, (2) Batteries, Charger, Lanyard, Nylon Pro Bag
Pallet Quantity	12
Carton Quantity	1

Operational

Recharge Time	0.5 hr
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	120V-AC Charger

Product Assets

[Catalog \[English\]](#)