



1500 Series Battery Cutter for CU/AL, Hard Case, No Batt/Chgr, Makita Power

By Burndy
Catalog # [PATCUT1500LCB](#)

PATRIOT® Series, 1500 Series Battery Cutter for Copper and Aluminum, Hard Case, No Battery, Makita Power

Features

- Variable speed trigger
- Forward/Reverse switch features a locking position
- Large, strategically placed, non-skid bumper
- LED Worklight
- Accepts 2.0Ah-6.0Ah Makita batteries

Application

Cutting

Specifications

Buy American Compliant	No
EU RoHS Indicator	No

Conductor

Crimping Ranges	Cutting Capacity: Aluminum up to 1500 kcmil, Copper (Soft Drawn) up to 1000 kcmil (Do Not Cut Steel or ACSR)
-----------------	--

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Package Height	0.000 in
Length	6 in
Package Weight	0.000 lb.
Package Length	0.000 in



Package Width	0.000 in
Weight	6.90 lb.
Height	15.5 in
Width	4.38 in
Dimensions	6 in x 4.38 in x 15.5 in

General

Application - For Use On	Aluminum, Copper Cable
Trade Name	PATRIOT®
Sub Brand	Cable cutter
Series	PATRIOT® Series
Tool Type	Battery Actuated Cutter
Container Type	Hard Case
UPC	621945541184
Type	Cutter
UPC 12 Digit	621945541184

Logistics

Minimum Pack Quantity	1
Package Contents	Cutter, Lanyard, Hard Case

Operational

Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	No Charger

Product Assets

[Catalog \[English\]](#)