



2156 Series Latch Head Battery Cutter, Hard Case, 5Ah Makita Batteries

By Burndy
Catalog # [PATCUT2156L5](#)

PATRIOT® Series, 2156 Series Latch Head Battery Cutter, Hard Case, 5.0Ah Makita Batteries



Features

- 180° head rotation
- Durable hardened steel blades
- Specialized latch head for mid-span cuts
- Mechanical ram release with no power consumption

Application

Cutting

Specifications

Buy American Compliant	No
EU RoHS Indicator	Under Review

Conductor

Crimping Ranges	• Cutting Capacity: Copper/Aluminum up to 2.0" • ACSR up to 2156 kcmil • Ground Rod up to 3/4" • Rebar up to 5/8" • Soft Steel Bolts up to 3/4" • Standard Guy up to 9/16" • EHS Guy Strand up to 9/16"
-----------------	---

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Length	16.46 in
Weight	14.10 lb.
Height	13.66 in
Width	3.27 in
Dimensions	16.46 in x 3.27 in x 13.66 in

Force Related

Crimp Force Capacity	10 ton
----------------------	--------

General

Application - For Use On	• ACSR, Aluminum, Copper Cable • Ground Rod • Rebar • Soft Steel Bolts • Standard Guy • EHS Guy Strand
Trade Name	PATRIOT®
Sub Brand	PATRIOT® CUTTER
Series	PATRIOT® Series
Tool Type	Battery Actuated Cutter
Container Type	Hard Case
UPC	621945471078
Type	Cutter
UPC 12 Digit	621945471078

Logistics

Minimum Pack Quantity	1
Package Contents	Cutter, (2) Batteries, Charger, Lanyard, Hard Case

Operational

Recharge Time	0.75 hr
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	120V-AC Charger

Product Assets

[Catalog \[English\]](#)