



PATRIOT® Series, 2156 Series Latch Head Battery Cutter, (2) 3.0Ah 18V Li-ion Batteries, 12V-DC Charger, Hard Case

By Burndy
Catalog # [PATCUT2156LIDC](#)

10T Latch Cut, ACSR, 3Ah, DC, HC

Features

- 180° head rotation
- Durable hardened steel blades
- Specialized latch head for mid-span cuts
- Mechanical ram release with no power consumption

Application

Cutting

Specifications

Standards - RoHS Compliance UI
Status

Conductor

- | | |
|-----------------|---|
| Crimping Ranges | <ul style="list-style-type: none">• Cutting Capacity: Copper/Aluminum up to 2.0"• ACSR up to 2156 kcmil• Ground Rod up to 3/4"• Rebar up to 5/8"• Soft Steel Bolts up to 3/4"• Standard Guy up to 9/16"• EHS Guy Strand up to 9/16" |
|-----------------|---|

Current

Operating Voltage 18 VDC

Dimensions

Dimension - Height mm	0 mm
Length	16.46 in
Weight	14.10 lb.
Height	13.66 in
Width	3.27 in
Dimensions	16.46 in x 3.27 in x 13.66 in



Force Related

Crimp Force Capacity 10 ton

General

- | | |
|--------------------------|--|
| Application - For Use On | <ul style="list-style-type: none">• ACSR, Aluminum, Copper Cable• Ground Rod• Rebar• Soft Steel Bolts• Standard Guy• EHS Guy Strand |
|--------------------------|--|

Trade Name	PATRIOT®
Series	PATRIOT® Series
Tool Type	Battery Actuated Cutter
Container Type	Hard Case
UPC	781810648865
Type	Cutter
UPC 12 Digit	781810648865
UPC 14 Digit GTIN	00781810648865

Logistics

Package Contents Cutter, (2) Batteries, Charger, Lanyard, Hard Case

Operational

Recharge Time	0.5 hr
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	12V-DC Charger

Product Assets

[Catalog \[English\]](#)