



2156 Series Latch Head Battery Cutter,
Hard Case, No Batt/Chgr, Makita Power

By Burndy
Catalog # [PATCUT2156LILCB](#)

PATRIOT® Series, 2156 Series Latch Head Battery Cutter, Hard
Case, No Batteries, Makita Power

Features

- 180° head rotation
- Durable hardened steel blades
- Specialized latch head for mid-span cuts
- Mechanical ram release with no power consumption

Application

Cutting

Specifications

Standards - RoHS Compliance UI
Status

Conductor

- Crimping Ranges
- Cutting Capacity:
Copper/Aluminum up to 2.0"
 - ACSR up to 2156 kcmil
 - Ground Rod up to 3/4"
 - Rebar up to 5/8"
 - Soft Steel Bolts up to 3/4"
 - Standard Guy up to 9/16"
 - EHS Guy Strand up to 9/16"

Current

Operating Voltage 18 VDC

Dimensions

Dimension - Height mm	0 mm
Length	16.46 in
Weight	14.10 lb.
Height	13.66 in
Width	3.27 in
Dimensions	16.46 in x 3.27 in x 13.66 in



Force Related

Crimp Force Capacity 10 ton

General

Application - For Use On

- ACSR, Aluminum, Copper
Cable
- Ground Rod
- Rebar
- Soft Steel Bolts
- Standard Guy
- EHS Guy Strand

Trade Name

Series

Tool Type

Container Type

UPC

Type

UPC 12 Digit

UPC 14 Digit GTIN

PATRIOT®

PATRIOT® Series

Battery Actuated Cutter

Hard Case

781810648872

Cutter

781810648872

00781810648872

Logistics

Minimum Pack Quantity 1
Package Contents Cutter, Lanyard, Hard Case

Operational

Recharge Time

Battery Type

Power Source

0.5 hr

3.0Ah 18V Li-Ion (Accepts
2.0Ah-6.0Ah Makita LI
Batteries)

No Charger

Product Assets

[Catalog \[English\]](#)