



2156 Series Latch Head Battery Cutter, Pro Bag, No Batt/Chgr, Makita Power

By Burndy
Catalog # [PATCUT2156LILCBPB](#)

PATRIOT® Series, 2156 Series Latch Head Battery Cutter, Pro Bag, No Batteries, Makita Power

Features

- 180° head rotation
- Durable hardened steel blades
- Specialized latch head for mid-span cuts
- Mechanical ram release with no power consumption

Application

Cutting

Specifications

Standards - RoHS Compliance UI
Status

Conductor

- Crimping Ranges
- Cutting Capacity: Copper/Aluminum up to 2.0"
 - ACSR up to 2156 kcmil
 - Ground Rod up to 3/4"
 - Rebar up to 5/8"
 - Soft Steel Bolts up to 3/4"
 - Standard Guy up to 9/16"
 - EHS Guy Strand up to 9/16"

Current

Operating Voltage 18 VDC

Dimensions

Length	16.46 in
Weight	14.10 lb.
Height	13.66 in
Width	3.27 in
Dimensions	16.46 in x 3.27 in x 13.66 in



Force Related

Crimp Force Capacity 10 ton

General

- Application - For Use On
- ACSR, Aluminum, Copper Cable
 - Ground Rod
 - Rebar
 - Soft Steel Bolts
 - Standard Guy
 - EHS Guy Strand
- Trade Name
- PATRIOT®
- Series
- PATRIOT® Series
- Tool Type
- Battery Actuated Cutter
- Container Type
- Nylon Pro Bag
- UPC
- 621945562264
- Type
- Cutter
- UPC 12 Digit
- 621945562264

Logistics

Minimum Pack Quantity	1
Package Contents	Cutter, Lanyard, Nylon Pro Bag
Pallet Quantity	12
Carton Quantity	1

Operational

Recharge Time	0.5 hr
Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source	No Charger

Product Assets

[Catalog \[English\]](#)