



4 Series Scissor Action CU/AL Battery Cutter Hard Case No Batt/Chgr Makita Power

By Burndy
Catalog # PATCUT4CUALLILCB

PATRIOT® Series, 4 Series Scissor Action, CU/AL Battery Cutter, Hard Case, No Batteries, Makita Power



Features

- Extra wide jaw opening
- Scissor action cutting jaws
- 355° head rotation
- Multi-position assist handle

Application

Cutting

Conductor

Crimping Ranges Cutting Capacity:
Copper/Aluminum up to 4.0" O.D.

Current

Operating Voltage 18 VDC

Dimensions

Dimension - Height mm 389.4 mm
Length 24.31 in
Weight 19.70 lb.
Height 15.33 in
Width 3.26 in
Dimensions 24.31 in x 3.26 in x 15.33 in

Force Related

Crimp Force Capacity 11 ton

General

Application - For Use On Aluminum, Copper Cable
Trade Name PATRIOT®
Series PATRIOT® Series
Tool Type Battery Actuated Cutter
Container Type Hard Case
UPC 621945437968
Type Cutter
UPC 12 Digit 621945437968
UPC 14 Digit GTIN 00621945437968

Logistics

Minimum Pack Quantity 1
Package Contents Cutter, Lanyard, Hard Case

Operational

Battery Type No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)

Power Source No Charger

Product Assets

[Catalog \[English\]](#)