



**PATRIOT® IN-LINE® 6-Ton Scissor Action, BG/D3 & O/D3 Crimp Jaws, CU/AL Cut Jaw, (2) 3.0Ah 18V Li-ion Batteries, 120V-AC Charger, Hard Case**

By Burndy  
Catalog # [PATMD13503A2](#)



PATMD-LW IN-LINE® 6T Scissor Action, BG/D3 & O/D3 Crimp Jaws, CU/AL Cut Jaw, 3Ah Li-ion, AC, Hard Case.

**Features**

- Interchangeable scissor action crimping and cutting jaws available
- 355° Head rotation
- Uses W and X dies
- Safety trigger lock and locking jaw tabs
- LED Worklight
- Accepts 2.0Ah-6.0Ah 18V lithium-ion Makita batteries

**Application**

Crimping and Cutting

**General**

|                          |                                                                                                                                                      |
|--------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| Application - For Use On | Interchangeable Jaws: Crimp: ACSR, Aluminum, Copper Code/Flex; Cut: ACSR (26/7), Aluminum (AAC), Copper (Soft Drawn), EHS Guy Wire (sold separately) |
| Battery Type             | 3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)                                                                                           |
| Catalog Number           | PATMD13503A2                                                                                                                                         |
| Container Type           | Hard Case                                                                                                                                            |
| Crimp Force Capacity     | 6 ton                                                                                                                                                |
| Die Type                 | W Die and X Die                                                                                                                                      |
| Power Source             | 120V-AC Charger                                                                                                                                      |
| Recharge Time            | 0.5 h                                                                                                                                                |
| Tool Type                | Battery Actuated Scissor Action                                                                                                                      |
| Trade Name               | PATRIOT® IN-LINE®                                                                                                                                    |
| Type                     | Crimper and Cutter                                                                                                                                   |
| UPC                      | 621945550735                                                                                                                                         |

**Dimensions**

|            |                               |
|------------|-------------------------------|
| Dimensions | 18.73 in x 4.375 in x 2.75 in |
| Height     | 2.75 in                       |
| Length     | 18.73 in                      |
| Weight     | 5.55 lb                       |
| Width      | 4.375 in                      |

**Conductor Related**

|                 |                                                                                                                                                                                                                                                                                                            |
|-----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Crimping Ranges | With Appropriate Jaw:<br>Crimping Capacity: Copper: #10 sol.-500 kcmil, Copper Flex: #8 AWG-350 kcmil, Aluminum: #14 sol.-350 kcmil, ACSR: #14 sol.-4/0 AWG; Cutting Capacity: ACSR (26/7) up to 556.5 kcmil, Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil, EHS Guy Wire up to 3/8" |
|-----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

**Logistics**

|                  |                                                                                   |
|------------------|-----------------------------------------------------------------------------------|
| Carton Quantity  | 1                                                                                 |
| Package Contents | Tool, BG/D3 and O/D3 Crimp Jaws, CU/AL Cut Jaw, (2) Batteries, Charger, Hard Case |
| Pallet Quantity  | 30                                                                                |

**Product Assets**

[Brochures - PATMD-LW Trifold Brochure](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50054521](#)  
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)  
[Specifications - PATMD13503A2](#)  
[Video - BURNDY PATMD-LW](#)



**A Hubbell brand**

©2025 Hubbell Incorporated. All rights reserved  
BRDY-PATMD13503A2-SPEC-EN | REV 7/2025