



IN-LINE 6T, BG/D3 & 430 Dieless Crimp Jaws, Util Bag, 5Ah Makita Batteries

By Burndy
Catalog # [PATMD18005A1](#)

PATRIOT® IN-LINE® Series, 6-Ton Scissor Action, BG/D3 & 430 Dieless Crimp Jaws, Utility Bag, 5.0Ah Makita Batteries



Features

- Interchangeable scissor action crimping and cutting jaws available
- 355° Head rotation
- Uses W and X dies
- Safety trigger lock and locking jaw tabs
- LED Worklight
- Accepts 2.0Ah-6.0Ah 18V lithium-ion Makita batteries

Application

Crimping and Cutting

Specifications

Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Conductor	
Crimping Ranges	• Copper: #8 AWG - 500 kcmil • Copper Flex: #8 AWG - 350 kcmil • AAC: #14 Sol. - 350 kcmil • ACSR: #14 sol. - 4/0 AWG • Utility distribution splices: #4 AWG - 3/0 AWG

Current

Operating Voltage	18 VDC
-------------------	--------

Dimensions

Length	18.1 in
--------	---------

Weight	5.55 lb.
Height	2.75 in
Width	4.375 in
Dimensions	18.1 in x 4.375 in x 2.75 in

Force Related

Crimp Force Capacity	6 ton
----------------------	-------

General

Trade Name	PATRIOT® IN-LINE®
Sub Brand	PATRIOT IN-LINE
Series	PATRIOT® IN-LINE® Series
Tool Type	Battery Actuated Scissor Action
Die Type	W Die and X Die
UPC	621945616448
Type	Crimper and Cutter

Logistics

Package Contents	Tool, BG/D3 and 430 Dieless Crimp Jaws, (2) Batteries, Charger, Utility Bag
Pallet Quantity	30
Carton Quantity	1

Operational

Recharge Time	0.75 hr
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)

Product Assets

[Catalog \[English\]](#)