



IN-LINE 6T, D3 Crimp Jaw, Pro Bag, 3Ah Makita Batteries

By Burndy
Catalog # [PATMD20003A3](#)

PATRIOT® IN-LINE® Series, 6-Ton Scissor Action, D3 Crimp Jaw, Pro Bag, 3.0Ah Makita Batteries

Features

- Interchangeable scissor action crimping and cutting jaws available
- 355° Head rotation
- Uses W and X dies
- Safety trigger lock and locking jaw tabs
- LED Worklight
- Accepts 2.0Ah-6.0Ah 18V lithium-ion Makita batteries

Application

Crimping and Cutting

Specifications

EU RoHS Indicator
Buy America(n) Qualified
UL Listed

Contact Manufacturer
Contact Manufacturer
No

Conductor

Crimping Ranges

- With Appropriate Jaw:
Crimping Capacity: Copper: #10 sol.-500 kcmil, Copper Flex: #8 AWG-350 kcmil, Aluminum: #14 sol.-350 kcmil, ACSR: #14 sol.-4/0 AWG
- Cutting Capacity: ACSR (26/7) up to 556.5 kcmil, Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil, EHS Guy Wire up to 3/8"

Current

Operating Voltage 18 VDC

Dimensions

Length 18.73 in
Weight 5.55 lb.
Height 2.75 in
Width 4.375 in
Dimensions 18.73 in x 4.375 in x 2.75 in



Force Related

Crimp Force Capacity 6 ton

General

Application - For Use On

- Interchangeable Jaws:
Crimp: ACSR, Aluminum, Copper Code/Flex
- Cut: ACSR (26/7), Aluminum (AAC), Copper (Soft Drawn), EHS Guy Wire (sold separately)

Trade Name PATRIOT® IN-LINE®
Sub Brand PATRIOT® IN-LINE® Crimp/Cut Kit

Series PATRIOT® IN-LINE® Series
Tool Type Battery Actuated Scissor Action

Container Type Nylon Pro Bag
Die Type W Die and X Die
UPC 621945626485
Type Crimper and Cutter
UPC 12 Digit 621945626485

Logistics

Minimum Pack Quantity 1
Package Contents Tool, D3 Crimp Jaw, (2) Batteries, Charger, Nylon Pro Bag

Pallet Quantity 12
Carton Quantity 1

Operational

Recharge Time 0.5 hr
Battery Type 3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)

Power Source 120V-AC Charger

Product Assets

[Catalog \[English\]](#)