



IN-LINE 6T, D3 Crimp, GUY Cut Jaws, Util Bag, 3Ah Makita Batteries

By Burndy
Catalog # [PATMD26003A1](#)

PATRIOT® IN-LINE® Series, 6-Ton Scissor Action, D3 Crimp, GUY Cut Jaws, Utility Bag, 3.0Ah Makita Batteries



Features

- Interchangeable scissor action crimping and cutting jaws available
- 355° Head rotation
- Uses W and X dies
- Safety trigger lock and locking jaw tabs
- LED Worklight
- Accepts 2.0Ah-6.0Ah 18V lithium-ion Makita batteries

Application

Crimping and Cutting

Conductor

Crimping Ranges

- With Appropriate Jaw:
Crimping Capacity: Copper: #10 sol.-500 kcmil, Copper Flex: #8 AWG-350 kcmil, Aluminum: #14 sol.-350 kcmil, ACSR: #14 sol.-4/0 AWG
- Cutting Capacity: ACSR (26/7) up to 556.5 kcmil, Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil, EHS Guy Wire up to 3/8"

Current

Operating Voltage 18 VDC

Dimensions

Weight 5.55 lb.
Height 2.75 in
Width 4.375 in
Length 19.25 in
Dimensions 19.25 in x 4.375 in x 2.75 in

Force Related

Crimp Force Capacity 6 ton

General

Tool Type Battery Actuated Scissor Action
Container Type Vinyl Utility Bag
Application - For Use On

- Interchangeable Jaws:
Crimp: ACSR, Aluminum, Copper Code/Flex
- Cut: ACSR (26/7), Aluminum (AAC), Copper (Soft Drawn), EHS Guy Wire (sold separately)

Die Type W Die and X Die
UPC 621945546547
Trade Name PATRIOT® IN-LINE®
Type Crimper and Cutter
UPC 12 Digit 621945546547
Series PATRIOT® IN-LINE® Series

Logistics

Pallet Quantity 30
Carton Quantity 1
Package Contents Tool, D3 Crimp Jaw, GUY Cut Jaw, (2) Batteries, Charger, Utility Bag

Operational

Recharge Time 0.5 hr
Battery Type 3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)

Power Source 120V-AC Charger

Product Assets

[Catalog \[English\]](#)