



## PATRIOT® IN-LINE® 6-Ton Scissor Action, O/D3 Crimp Jaw, (2) 5.0Ah 18V Li-ion Batteries, 120V-AC Charger, Nylon Pro Bag

By Burndy

Catalog # [PATMD30005A3](#)

PATMD-LW IN-LINE® 6T Scissor Action, O/D3 Crimp Jaw, 5Ah Li-Ion, AC, Nylon Pro Bag.

### Features

- Interchangeable scissor action crimping and cutting jaws available
- 355° Head rotation
- Uses W and X dies
- Safety trigger lock and locking jaw tabs
- LED Worklight
- Accepts 2.0Ah-6.0Ah 18V lithium-ion Makita batteries

### Application

Crimping and Cutting

### General

|                          |                                                                                                                                                      |
|--------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| Application - For Use On | Interchangeable Jaws: Crimp: ACSR, Aluminum, Copper Code/Flex; Cut: ACSR (26/7), Aluminum (AAC), Copper (Soft Drawn), EHS Guy Wire (sold separately) |
| Battery Type             | 5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)                                                                                           |
| Catalog Number           | PATMD30005A3                                                                                                                                         |
| Container Type           | Nylon Pro Bag                                                                                                                                        |
| Crimp Force Capacity     | 6 ton                                                                                                                                                |
| Die Type                 | W Die and X Die                                                                                                                                      |
| EU RoHS Indicator        | Contact Manufacturer                                                                                                                                 |
| Power Source             | 120V-AC Charger                                                                                                                                      |
| Recharge Time            | 0.5 h                                                                                                                                                |
| Sub Brand                | PATRIOT® IN-LINE® Crimp/Cut Kit                                                                                                                      |
| Tool Type                | Battery Actuated Scissor Action                                                                                                                      |
| Trade Name               | PATRIOT® IN-LINE®                                                                                                                                    |
| Type                     | Crimper and Cutter                                                                                                                                   |
| UPC                      | 621945626461                                                                                                                                         |

### Dimensions

|            |                               |
|------------|-------------------------------|
| Dimensions | 18.73 in x 4.375 in x 2.75 in |
| Height     | 2.75 in                       |



|        |          |
|--------|----------|
| Length | 18.73 in |
| Weight | 5.55 lb  |
| Width  | 4.375 in |

### Electrical Ratings

|                   |        |
|-------------------|--------|
| Operating Voltage | 18 VDC |
|-------------------|--------|

### Conductor Related

|                 |                                                                                                                                                                                                                                                                                                            |
|-----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Crimping Ranges | With Appropriate Jaw:<br>Crimping Capacity: Copper: #10 sol.-500 kcmil, Copper Flex: #8 AWG-350 kcmil, Aluminum: #14 sol.-350 kcmil, ACSR: #14 sol.-4/0 AWG; Cutting Capacity: ACSR (26/7) up to 556.5 kcmil, Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil, EHS Guy Wire up to 3/8" |
|-----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

### Certifications And Compliance

|                          |                      |
|--------------------------|----------------------|
| Buy America(n) Qualified | Contact Manufacturer |
| UL Listed                | No                   |

### Logistics

|                       |                                                             |
|-----------------------|-------------------------------------------------------------|
| Carton Quantity       | 1                                                           |
| Minimum Pack Quantity | 1                                                           |
| Package Contents      | Tool, O/D3 Crimp Jaw, (2) Batteries, Charger, Nylon Pro Bag |
| Pallet Quantity       | 12                                                          |

### Product Assets

[Brochures - PATMD-LW Trifold Brochure](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50106124](#)  
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)



A Hubbell brand