



**PATRIOT® IN-LINE® 6-Ton Scissor Action, O/D3 Crimp Jaw, GUY Cut Jaw, (2) 5.0Ah 18V Li-ion Batteries, 120V-AC Charger, Utility Bag**

By Burndy  
Catalog # [PATMD36005A1](#)

PATMD-LW IN-LINE® 6T Scissor Action, O/D3 Crimp Jaw, GUY Cut Jaw, 5Ah Li-ion, AC, Utility Bag.

**Features**

- Interchangeable scissor action crimping and cutting jaws available
- 355° Head rotation
- Uses W and X dies
- Safety trigger lock and locking jaw tabs
- LED Worklight
- Accepts 2.0Ah-6.0Ah 18V lithium-ion Makita batteries

**Application**

Crimping and Cutting

**General**

|                          |                                                                                                                                                      |
|--------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| Application - For Use On | Interchangeable Jaws: Crimp: ACSR, Aluminum, Copper Code/Flex; Cut: ACSR (26/7), Aluminum (AAC), Copper (Soft Drawn), EHS Guy Wire (sold separately) |
| Battery Type             | 5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)                                                                                           |
| Catalog Number           | PATMD36005A1                                                                                                                                         |
| Container Type           | Vinyl Utility Bag                                                                                                                                    |
| Crimp Force Capacity     | 6 ton                                                                                                                                                |
| Die Type                 | W Die and X Die                                                                                                                                      |
| Power Source             | 120V-AC Charger                                                                                                                                      |
| Recharge Time            | 0.75 h                                                                                                                                               |
| Tool Type                | Battery Actuated Scissor Action                                                                                                                      |
| Trade Name               | PATRIOT® IN-LINE®                                                                                                                                    |
| Type                     | Crimper and Cutter                                                                                                                                   |
| UPC                      | 621945546578                                                                                                                                         |

**Dimensions**

|            |                               |
|------------|-------------------------------|
| Dimensions | 19.25 in x 4.375 in x 2.75 in |
|------------|-------------------------------|



|        |          |
|--------|----------|
| Height | 2.75 in  |
| Length | 19.25 in |
| Weight | 5.55 lb  |
| Width  | 4.375 in |

**Electrical Ratings**

|                   |        |
|-------------------|--------|
| Operating Voltage | 18 VDC |
|-------------------|--------|

**Conductor Related**

|                 |                                                                                                                                                                                                                                                                                                            |
|-----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Crimping Ranges | With Appropriate Jaw:<br>Crimping Capacity: Copper: #10 sol.-500 kcmil, Copper Flex: #8 AWG-350 kcmil, Aluminum: #14 sol.-350 kcmil, ACSR: #14 sol.-4/0 AWG; Cutting Capacity: ACSR (26/7) up to 556.5 kcmil, Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil, EHS Guy Wire up to 3/8" |
|-----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

**Logistics**

|                  |                                                                        |
|------------------|------------------------------------------------------------------------|
| Carton Quantity  | 1                                                                      |
| Package Contents | Tool, O/D3 Crimp Jaw, GUY Cut Jaw, (2) Batteries, Charger, Utility Bag |
| Pallet Quantity  | 30                                                                     |

**Product Assets**

- [Brochures - PATMD-LW Trifold Brochure](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
- [Specifications - PATMD36005A1](#)
- [Video - BURNDY EHS Guy Wire cutting jaw](#)
- [Video - BURNDY PATMD-LW](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
BRDY-PATMD36005A1-SPEC-EN | REV 7/2025