



**PATRIOT® IN-LINE® 6-Ton Scissor
Action, O/D3 & 430 Dieless Crimp
Jaw, (2) 3.0Ah 18V Li-ion Batteries,
120V-AC Charger, Utility Bag**

By Burndy
Catalog # [PATMD38003A1](#)



PATMD-LW IN-LINE® O/D3 & 430 Dieless Crimp Jaws, 3Ah Li-ion, AC, Vinyl Utility Bag.

Features

- Interchangeable scissor action crimping and cutting jaws available
- 355° Head rotation
- Uses W and X dies
- Safety trigger lock and locking jaw tabs
- LED Worklight
- Accepts 2.0Ah-6.0Ah 18V lithium-ion Makita batteries

Application

Crimping and Cutting

General

Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PATMD38003A1
Crimp Force Capacity	6 ton
Die Type	W Die and X Die
EU RoHS Indicator	Contact Manufacturer
Recharge Time	0.5 h
Sub Brand	PATRIOT IN-LINE
Tool Type	Battery Actuated Scissor Action
Trade Name	PATRIOT® IN-LINE®
Type	Crimper and Cutter
UPC	621945616455

Dimensions

Dimensions	18.1 in x 4.375 in x 2.75 in
Height	2.75 in
Length	18.1 in

Weight	5.55 lb
Width	4.375 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #8 AWG - 500 kcmil; Copper Flex: #8 AWG - 350 kcmil; AAC: #14 Sol. - 350 kcmil; ACSR: #14 sol. - 4/0 AWG; Utility distribution splices: #4 AWG - 3/0 AWG
-----------------	---

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Carton Quantity	1
Package Contents	Tool, O/D3 & 430 Dieless Crimp Jaw, (2) Batteries, Charger, Utility Bag
Pallet Quantity	30

Product Assets

[Brochures - PATMD-LW Trifold Brochure](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50054521](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Specifications - PATMD38003A1](#)
[Video - BURNDY PATMD-LW](#)