



PATRIOT® IN-LINE® Series, 6-Ton Scissor Action, D3 Crimp Jaw, ACSR Cut Jaw, (2) 5.0Ah 18V Li-ion Batteries, 120V-AC Charger, Utility Bag

By Burndy
Catalog # PATMD66LW5WCJ

6T IN-LINE® D3 ACSR 5Ah AC UB



Features

- Interchangeable scissor action crimping and cutting jaws available
- 355° Head rotation
- Uses W and X dies
- Safety trigger lock and locking jaw tabs
- LED Worklight
- Accepts 2.0Ah-6.0Ah 18V lithium-ion Makita batteries

Application

Crimping and Cutting

Conductor

- Crimping Ranges
- With Appropriate Jaw:
Crimping Capacity: Copper: #10 sol.-500 kcmil, Copper Flex: #8 AWG-350 kcmil, Aluminum: #14 sol.-350 kcmil, ACSR: #14 sol.-4/0 AWG
 - Cutting Capacity: ACSR (26/7) up to 556.5 kcmil, Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil, EHS Guy Wire up to 3/8"

Current

Operating Voltage18 VDC

Dimensions

Length17.85 in
Weight5.55 lb.
Height2.75 in
Width4.375 in
Dimensions17.85 in x 4.375 in x 2.75 in

Force Related

Crimp Force Capacity6 ton

General

Application - For Use On

- Interchangeable Jaws:
Crimp: ACSR, Aluminum, Copper Code/Flex
- Cut: ACSR (26/7), Aluminum (AAC), Copper (Soft Drawn), EHS Guy Wire (sold separately)

Trade NamePATRIOT® IN-LINE®
SeriesPATRIOT® IN-LINE® Series
Tool TypeBattery Actuated Scissor Action
Container TypeVinyl Utility Bag
Die TypeW Die and X Die
UPC621945480940
TypeCrimper and Cutter
UPC 12 Digit621945480940

Logistics

Package ContentsTool, D3 Crimp Jaw, ACSR Cut Jaw, (2) Batteries, Charger, Utility Bag
Pallet Quantity30
Carton Quantity1

Operational

Recharge Time0.75 hr
Battery Type5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source120V-AC Charger

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)