



IN-LINE 6T, Crimper Jaw Permanent D3 Groove Only (Jaw Only)

By Burndy
Catalog # [PATMD66LWJAW](#)

PATRIOT® IN-LINE® Series, 6-Ton Scissor Action, D3 Crimp Jaw with Permanent Groove Only (Jaw Only)

Features

- Crimp jaw with permanent D3 grooves
- Interchangeable scissor action jaw
- Locking jaw tabs
- Uses W and X dies
- for PATMD-LW series batteries

Application

Crimping and Cutting

Conductor

Crimping Ranges	Copper: #10 sol. - 500 kcmil, Copper Flex: #8 AWG - 350 kcmil, Aluminum: #14 sol. - 350 kcmil, ACSR: #14 sol. - 4/0 AWG
-----------------	--

Dimensions

Weight	2 lb.
Height	1.0625 in
Width	4.27 in
Length	4.21 in



Dimensions	4.21 in x 4.27 in x 1.0625 in
------------	-------------------------------

Force Related

Crimp Force Capacity	6 ton
----------------------	-------

General

Tool Type	Crimper Jaw
Application - For Use On	Crimping with Permanent D3 Die Groove, W & X Dies
Die Type	W Die and X Die
UPC	621945483491
Trade Name	PATRIOT® IN-LINE®
Type	Crimper and Cutter
UPC 12 Digit	621945483491
Series	PATRIOT® IN-LINE® Series

Logistics

Package Contents	D3 Crimper Jaw for PATMD-LW Tool
------------------	----------------------------------

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)