



IN-LINE 82" F711 Pole Tool, Angled, O/D3 Crimp Jaw, 3Ah Makita Batteries

By Burndy
Catalog # PATMD6882ALLIF

PATRIOT® IN-LINE® Series, 82" F711 Pole Tool with Angled Head, O/D3 Crimp Jaw, 3.0Ah Makita Batteries



Features

- Interchangeable scissor action crimping and cutting jaws available
- 355° Head rotation
- Uses W and X dies
- Safety trigger lock and locking jaw tabs
- Accepts 2.0Ah-6.0Ah 18V lithium-ion Makita batteries

Application

Crimping and Cutting

Specifications

Standards - RoHS Compliance UI
Status

Conductor

- Crimping Ranges
- With Appropriate Jaw:
Crimping Capacity: Copper: #10 sol.-500 kcmil, Copper Flex: #8 AWG-350 kcmil, Aluminum: #14 sol.-350 kcmil, ACSR: #14 sol.-4/0 AWG
 - Cutting Capacity: ACSR (26/7) up to 556.5 kcmil, Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil, EHS Guy Wire up to 3/8"

Dimensions

Length	82 in
Dimension - Height inch	82
Dimension - Width inch	4.375
Weight	13 lb.
Height	2.75 in
Width	4.375 in
Dimension - Depth inch	2.75

Dimensions 82 in x 4.375 in x 2.75 in

Force Related

Crimp Force Capacity 6 ton

General

- Application - For Use On
- Interchangeable Jaws:
Crimp: ACSR, Aluminum, Copper Code/Flex
 - Cut: ACSR (26/7), Aluminum (AAC), Copper (Soft Drawn), EHS Guy Wire (sold separately)
- Trade Name PATRIOT® IN-LINE®
Series PATRIOT® IN-LINE® Series
Tool Type Battery Actuated Scissor Action
Container Type No Case/Bag
Die Type W Die and X Die
UPC 621945461802
Type Crimper and Cutter
UPC 12 Digit 621945461802

Logistics

Minimum Pack Quantity 1
Package Contents Tool, O/D3 Crimp Jaw, (2) Batteries, Charger
Pallet Quantity 28
Carton Quantity 1

Operational

Recharge Time 0.5 hr
Battery Type 3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Power Source 120V-AC Charger

Product Assets

[Catalog \[English\]](#)