



IN-LINE 6T, O/D3 Crimp Jaw, Util Bag, 5Ah Makita Batteries

By Burndy
Catalog # [PATMD68LW5](#)

6T IN-LINE® O/D3 5Ah AC UB



Features

- Interchangeable scissor action crimping and cutting jaws available
- 355° Head rotation
- Uses W and X dies
- Safety trigger lock and locking jaw tabs
- LED Worklight
- Accepts 2.0Ah-6.0Ah 18V lithium-ion Makita batteries

Application

Crimping and Cutting

Specifications

Buy American Compliant
EU RoHS Indicator
Buy America(n) Qualified

Contact Manufacturer
Contact Manufacturer
Contact Manufacturer

Conductor

Crimping Ranges

- With Appropriate Jaw:
Crimping Capacity: Copper: #10 sol.-500 kcmil, Copper Flex: #8 AWG-350 kcmil, Aluminum: #14 sol.-350 kcmil, ACSR: #14 sol.-4/0 AWG
- Cutting Capacity: ACSR (26/7) up to 556.5 kcmil, Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil, EHS Guy Wire up to 3/8"

Current

Operating Voltage 18 VDC

Dimensions

Length 18.73 in
Weight 5.55 lb.
Height 4.38 in
Width 2.75 in

Dimensions

18.73 in x 2.75 in x 4.38 in

Force Related

Crimp Force Capacity 6 ton

General

Application - For Use On

- Interchangeable Jaws:
Crimp: ACSR, Aluminum, Copper Code/Flex
- Cut: ACSR (26/7), Aluminum (AAC), Copper (Soft Drawn), EHS Guy Wire (sold separately)

Trade Name
Sub Brand
Series
Tool Type

PATRIOT® IN-LINE®
PATRIOT® IN-LINE® CRIMPER
PATRIOT® IN-LINE® Series
Battery Actuated Scissor Action

Container Type
Die Type
UPC
Type
UPC 12 Digit

Vinyl Utility Bag
W Die and X Die
621945477124
Crimper and Cutter
621945477124

Logistics

Minimum Pack Quantity
Package Contents

1
Tool, O/D3 Crimp Jaw, (2)
Batteries, Charger, Utility Bag

Pallet Quantity
Carton Quantity

30
1

Operational

Recharge Time
Battery Type

0.75 hr
5.0Ah 18V Li-Ion (Accepts
2.0Ah-6.0Ah Makita LI
Batteries)

Power Source

120V-AC Charger

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)



A Hubbell brand