



IN-LINE 6T, O/D3 Crimp, CU/AL Cut Jaws, Util Bag, 5Ah Makita Batteries

By Burndy
Catalog # [PATMD68LW5WCCJ](#)

PATRIOT® IN-LINE® Series, 6-Ton Scissor Action, O/D3 Crimp, CU/AL Cut Jaws, Utility Bag, 5.0Ah Makita Batteries

Features

- Interchangeable scissor action crimping and cutting jaws available
- 355° Head rotation
- Uses W and X dies
- Safety trigger lock and locking jaw tabs
- LED Worklight
- Accepts 2.0Ah-6.0Ah 18V lithium-ion Makita batteries

Application

Crimping and Cutting

Conductor

Crimping Ranges

- With Appropriate Jaw:
Crimping Capacity: Copper: #10 sol.-500 kcmil, Copper Flex: #8 AWG-350 kcmil, Aluminum: #14 sol.-350 kcmil, ACSR: #14 sol.-4/0 AWG
- Cutting Capacity: ACSR (26/7) up to 556.5 kcmil, Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil, EHS Guy Wire up to 3/8"

Dimensions

Length	18.73 in
Weight	5.55 lb.
Height	2.75 in
Width	4.375 in
Dimensions	18.73 in x 4.375 in x 2.75 in

Force Related

Crimp Force Capacity	6 ton
----------------------	-------



General

Application - For Use On

- Interchangeable Jaws:
Crimp: ACSR, Aluminum, Copper Code/Flex
- Cut: ACSR (26/7), Aluminum (AAC), Copper (Soft Drawn), EHS Guy Wire (sold separately)

Trade Name

PATRIOT® IN-LINE®

Series

PATRIOT® IN-LINE® Series

Tool Type

Battery Actuated Scissor Action

Container Type

Vinyl Utility Bag

Die Type

W Die and X Die

UPC

621945528741

Type

Crimper and Cutter

UPC 12 Digit

621945528741

Logistics

Minimum Pack Quantity

1

Package Contents

Tool, O/D3 Crimp Jaw, CU/AL Cut Jaw, (2) Batteries, Charger, Utility Bag

Pallet Quantity

30

Carton Quantity

1

Operational

Recharge Time

0.75 hr

Battery Type

5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)

Power Source

120V-AC Charger

Product Assets

[Catalog \[English\]](#)



A Hubbell brand